

TECHSPEC[®] 50mm Diameter, T-Mount Thick Optic Mount



50mm Diameter, T-Mount Achromat/Thick Lens Mount, #88-944



Stock **#88-944** 3 In Stock

-

1

+

S\$151⁻²⁰

ADD TO CART

Volume Pricing	
Qty 1-4	S\$151.20 each
Qty 5-9	S\$131.46 each
Qty 10-25	S\$120.82 each
Need More?	Request Quote

Product Downloads

General

Type:

Fixed

Type of Optics:

Circular

Function:

Physical & Mechanical Properties

32.5	Extension Length (mm):
Black Anodized Aluminum (6061 T6)	Construction:
35.95	Total Length (mm):
53.0	Outer Diameter (mm):
38.0	Clear Aperture CA (mm):
18.5	Max. Thickness of Compatible Optics (mm):
5.0	Min. Thickness of Compatible Optics (mm):

Threading & Mounting

50.0	Diameter of Compatible Optics (mm):
T-Mount	Thread Type:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:


Product Details

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

Note: [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

Technical Information







S-Thread Simple / Thin Lens Mount



S-Thread Simple /Thin Lens Mount



S-Thread Achromat / Thick Lens Mount





#58-741

