

TECHSPEC[®] 50mm Diameter x -125 FL, VIS-NIR, Inked, Plano-Concave Lens



TECHSPEC VIS-NIR Coated Plano-Concave (PCV) Lenses



Stock **#45-926-INK** 10-15 DAYS

[Other Coating Options](#)

− 1 +

S\$119.63

ADD TO CART

Qty 1-9

S\$119.63

Qty 10+

S\$107.66

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00 ±0.025

Effective Focal Length EFL (mm):

-125.00
Substrate: N-BK7
f#: 2.5
Numerical Aperture NA: 0.20
Coating: VIS-NIR (400-1000nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -128.30
Bevel: Protective bevel as needed
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 49.00
Coating Specification: R_{abs} ≤0.25% @ 880nm R_{avg} ≤1.25% @ 400 - 870nm R_{avg} ≤1.25% @ 890 - 1000nm
Edge Thickness ET (mm): 9.87
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -64.60
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View