

# 50mm Travel, Metric Micrometer, Solid Top Ball Bearing Stage



Solid Top Stage



Stock **#38-178** 3-5 DAYS

- 1 +

**S\$1,519.60**

ADD TO CART

|             |
|-------------|
| Qty 1+      |
| S\$1,519.60 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

## Get Product Downloads

Type of Movement:  
Linear (X)

Guide System:  
Ball Bearing

Type of Drive:  
Metric Micrometer

Drive Orientation:  
Center Drive

|                                                                   |
|-------------------------------------------------------------------|
| <b>Type:</b><br>English                                           |
| <b>Stage Size (mm):</b><br>127 x 127                              |
| <b>Travel (mm):</b><br>50                                         |
| <b>Construction:</b><br>Aluminium Stage                           |
| <b>Graduation (mm):</b><br>0.01                                   |
| <b>Height (inches):</b><br>1.00                                   |
| <b>Height (mm):</b><br>25.4                                       |
| <b>Load Capacity, Normal (lbs):</b><br>105                        |
| <b>Note:</b><br>Solid Top                                         |
| <b>Stage Size (inches):</b><br>5.00 x 5.00                        |
| <b>Straight Line Accuracy (inches):</b><br>0.00008/inch of travel |
| <b>Weight (lbs):</b><br>2.7                                       |
| <b>Thrust Capacity, T<sub>a</sub> (lbs):</b><br>30                |
| <b>Thrust Capacity, T<sub>b</sub> (lbs):</b><br>2.5               |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |