

TECHSPEC[®] 514.5nm CWL, 25mm Dia, 3.0 FWHM, Hard Coated Laser Clean-Up Filter



Stock #68-874 3-5 DAYS

[Additional Bandwidths](#)

-

1

+

S\$285.36

ADD TO CART

Qty 1+

S\$285.36

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Angle of Incidence (°):
0.00

Optical Density OD (Average):
≥4.0

Center Wavelength CWL (nm):
514.50

Design Wavelength DWL (nm): 514.5
Full Width-Half Max FWHM (nm): 3.00
Full Width-Half Max FWHM Tolerance (nm): ±1.0
Substrate: Fused Silica (Corning 7980)
Minimum Transmission (%): >80
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Blocking Wavelength Range (nm): 400 - 509 & 520 - 700
Clear Aperture (%): >90
Transmitted Wavefront, RMS: λ/4
Parallelism (arcsec): <30
Angle of Incidence Tolerance (°): ±5.0
Mount Thickness (mm): 3.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View