

530nm, LED Linear Axial Diffuse Light

See More by [Advanced Illumination](#)



Stock #66-875 [CONTACT US](#)

1 **S\$4,792.25**

ADD TO CART

Qty 1+

S\$4,792.25

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Green

Model Number:
DL110-530-IC

Operating Temperature (°C):
0 to 60

Wavelength (nm):
530.00

Weight (lbs):

1.3

Working Distance (mm):

12.7 - 50

LED Lifetime (hours):

50,000

Power Supply:

Power Supply Required and Sold Separately.

USA: [#66-855](#)Europe: [#66-855](#)Japan: [#66-855](#)Korea: [#33-773](#)China: [#66-855](#)**Light Distribution (%):**

±10

Number of LEDs:

12 High Brightness

Length of Cable (m):

2

Maximum Trigger Frequency (Hz):

30.00

Strobe Duration (µs):

30 - 300

Type of Illumination:

LED Illuminator

Note:Optional Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are Available**Manufacturer:**

Advanced Illumination

Geometry:

Diffuse Axial

Illumination Mode:

Constant

Regulatory Compliance

RoHS 2015:[Compliant](#)**Certificate of Conformance:**[View](#)**Reach 233:**[Contains SVHC\(s\)](#)