

TECHSPEC[®] 5mm Length, C-Mount Extension Tube



Stock **#54-628** 20+ In Stock

-

1

+

S\$45⁻¹⁸

ADD TO CART

Volume Pricing	
Qty 1-4	S\$45.18 each
Qty 5-9	S\$40.78 each
Qty 10-25	S\$37.79 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Extension Tube

Type:

Extension Tube (Fixed)

Function:

Physical & Mechanical Properties	
5.0	Extension Length (mm):
9.0	Total Length (mm):
30.0	Outer Diameter (mm):
22.0	Clear Aperture CA (mm):
Threading & Mounting	
C-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

PRODUCT DETAILS

- Used for Adding a Fixed Tube Extension to Optical Systems
 - Feature Male/Female Threads at Opposite Ends
 - Black Anodized Aluminum Construction
- TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

TECHNICAL INFORMATION

C-Mount Dimensions

1-32 C-Mount
Female Thread

