

6" x 6", Red 660nm, UltraSeal Washdown Backlight

See More by [Advanced Illumination](#)



Advanced Illumination UltraSeal Washdown Backlights

Stock **#18-619** 3-5 DAYS

⊖ 1 ⊕

S\$1,950.25

ADD TO CART

Qty 1+

S\$1,950.25

Volume Pricing

[Request Quote](#)

Get Product Downloads

Color:
Red

Input Voltage (V):
24V

Model Number:
BL245-06066601C

Operating Temperature (°C):
0 - 60

Dimensions (mm):

173.0 x 173.0 x 24.0
Wavelength (nm): 660.00
Weight (g): 698
LED Lifetime (hours): 50000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Active Area (inches): 6 x 6
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Constant
Environmental Rating: IP69K
Minimum Input Current: 1.08A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)