

600 lp/mm, 1" x 3", FS w/ Fluorescent, Ronchi



Stock #57-883 CLEARANCE 1 In Stock

-

1

+

S\$1,366^{.55}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$1,366.55 each
Qty 5+	S\$1,298.29 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

Physical & Mechanical Properties

3.00

Length (inches):

12.7 x25.4

Pattern Size (mm):

Thickness (mm):

1.10	
	Width (inches):
1.00	
Optical Properties	
	Coating:
Vacuum Deposited Chrome Fluorescent Peak Excitation @ 365 nm; Fluorescent Peak Emission @ 550 nm	
	Frequency (lp/mm):
600.00	
	Substrate:
Fused Silica with Fluorescent Backing	
	Optical Density OD (Average):
3.00	
Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 240:
Compliant	

PRODUCT DETAILS

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
 - Ideal for Reticle and Field Calibration Requirements
 - Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and Opal.
- Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.