

## 60mm, Metric Rotary Stage



60mm Dia. Precision Rotary Stage, #55-029



Stock **#55-029** **20+ In Stock**

⊖ 1 ⊕ **\$\$672<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1-4	<b>\$\$672.00</b> each
Qty 5+	<b>\$\$592.90</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Metric **Type:**

### Physical & Mechanical Properties

Rotary **Type of Movement:**

**Guide System:**

Slide-Fit

60 Dia. **Stage Size (mm):**

±5 (Fine), 360 (Coarse) **Travel (°):**

M16 x 1 **Center Hole:**

20 **Concentricity (µm):**

Aluminium Stage **Construction:**

5' **Increments:**

5 **Load Capacity (kg):**

23.0 **Travel Per Knob Rotation (arcmin):**

0.25 **Weight (kg):**

### Hardware & Interface Connectivity

Metric Micrometer **Type of Drive:**

### Threading & Mounting

(1) M16 x 1, (4) M4 x 0.7, (4) M3 x 0.5 **Mounting Threads:**

### Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 247:**

## Product Details

- Precision Micrometer Drive and Manual Drive Options
- 360° Coarse Rotation
- Micrometer Drive Models Provide ±5° Fine Rotation
- Black Anodized Aluminum Construction

Metric Rotary Stages feature slide-fit guide system, enabling 360° course rotation. Micrometer drive models feature a precision metric micrometer and a switchable clamp mechanism to change between course and fine movements for precise ±5° angular adjustment at any position. The manual drive model provides a smooth manual adjustment with 360° coarse movement, 1° increments. Metric Rotary Stages feature a locking mechanism to fix the stage position. For breadboard mounting, use the [Metric Base Plates](#).

## Technical Information

