

630nm LED Ring Light



Stock #63-304 3-5 DAYS

1

S\$1,051.25

ADD TO CART

Qty 1+
S\$1,051.25

Volume Pricing
Request Quote

Get Product Downloads

Color: Red
Diameter (mm): 70.80
Full Width-Half Max FWHM (nm): 30.00
Height (mm): 17.00
Mounting Threads: (4) M3

Wavelength (nm): 630.00
LED Lifetime (hours): 100,000
Power Supply: Power Supply Required and Sold Separately: USA: #59-433 Europe: Not Available Japan: #59-433 Korea: Not Available China: #59-433
Spot Size at 40mm Working Distance (mm): 100.00
Irradiance at 40mm (W/m²): 80.00
Type of Illumination: LED Illuminator
Geometry: Ring Light
Illumination Mode: Strobed or Constant

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View