

[See all 6 Products in Family](#)

**TECHSPEC® 63.5mm Length, M6 Thread, Adjustable Post Holder**



TECHSPEC Adjustable Height Post Holders

Stock #84-350 **20+ In Stock**

⊖ 1 ⊕ **\$196<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-9	<b>\$196.00</b> each
Qty 10+	<b>\$176.40</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Metric **Type:**

**Physical & Mechanical Properties**

63.50 **Length (mm):**

10.00 **Travel (mm):**

**Threading & Mounting**

---

M6 x 1.0 **Mounting Threads:**

---

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

---

## Product Details

- English and Metric Versions
- 1/4-20 Base for English Version and M6 x 1 Base for Metric Version
- Provides Vertical Translation
- Compatible With 0.5" (12.7mm) Posts

TECHSPEC® Adjustable Height Post Holders are inexpensive alternatives to Z-axis and vertical stages. Featuring an adjustable ring that, when rotated, provides vertical translation, these post holders are ideal for applications that require vertical translation, but do not require the level of precision provided by a stage. These post holders are compatible with 0.5" (12.7mm) posts. TECHSPEC® Adjustable Height Post Holders have a 1/4 - 20 base for the English version and an M6 x 1 base for the Metric version. The post holders are available in three different lengths for both the English and the Metric versions.