

64L x 41mm Dia. Lens Tube, IP65/67

See More by [IDS Imaging Development Systems](#)



#62-066

Stock **#62-066** 4 In Stock

-

1

+

S\$165^{.30}

ADD TO CART

Volume Pricing	
Qty 1+	S\$165.30 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

General

Camera Accessory

Type:

Note:

Accommodate C-Mount lens up to 51mm in length
(without thread), 35mm in diameter

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	REACH 241:
-----------	------------

PRODUCT DETAILS

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.

TECHNICAL INFORMATION

EO USB2.0 Harsh Environment (HE)
Camera with Lens Enclosure

