

660nm, Strobed, Extended Working Distance 4" LED Ring Light w/ Barrel Mount

See More by [Advanced Illumination](#)



Stock #83-247 [CONTACT US](#)

-

1

+

S\$1,249.90

ADD TO CART

Qty 1+
S\$1,249.90

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

- Color:

Red
- Diameter (mm):

100.00
- Inner Diameter (mm):

55.5
- Model Number:

RL4260B-660EDF-IS

Mount: 3 screw Barrel Mount
Operating Temperature (°C): 0 to 65
Outer Diameter (mm): 100.00
Mounting Threads: M4 x4
Wavelength (nm): 660.00
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of LEDs: 60.00
Number of Channels: 1.00
Field Coverage (mm): 50.8 (2")
Strobe Duration (µs): 30 - 300
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Ring Light
Illumination Mode: Strobed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)