

TECHSPEC® 70mm, 180mm Radius, English Goniometer



70mm, 180mm Radius, English Goniometer

Stock #66-534 3-5 DAYS

⊖ 1 ⊕

S\$1,054.15

ADD TO CART

Qty 1-2
S\$1,054.15
Qty 3+
S\$923.07
Volume Pricing
Request Quote

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type:
English

Stage Size (mm):

70 x 70
Travel (°): ±8
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 6
Mounting Threads: (9) ¼-20, (4) 6-32, (8) 2-56
Radius R (mm): 180
Resolution (arcmin): 5
Stage Size (inches): 2.75 x 2.75
Weight (kg): 0.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant