

TECHSPEC[®] 70mm, 180mm Radius, Metric Goniometer



TECHSPEC[®] Goniometers



+1

Stock #66-537 2 In Stock

-

1

+

S\$1,141^{.00}

ADD TO CART

Volume Pricing	
Qty 1-2	S\$1,141.00 each
Qty 3+	S\$999.18 each
Need More?	Request Quote

Product Downloads

General	
Type:	Metric
Resolution (arcmin):	5
Physical & Mechanical Properties	
Type of Movement:	

[illegible]

R (mm)	English Stage	Metric Stage	A (mm)	B (mm)	C (mm)
120	#6-S32	#6-S25	130	100	12.5
150	#6-S33	#6-S36	160	130	12.4
180	#6-S34	#6-S37	190	160	12.4