

TECHSPEC® 75 x 75mm 40R/60T, NIR Plate Beamsplitter



Visible and NIR Plate Beamsplitters

Stock **#68-398** 3-5 DAYS

⊖ 1 ⊕ **S\$485.75**

ADD TO CART

Qty 1-5

S\$485.75

Qty 6+

S\$388.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
45

Clear Aperture (%):
>85

Coating Specification:
Surface 1: 40/60 ±5% @ 900nm, ±10% @ 700 - 1100nm

Surface 2: AR $R_{avg} \leq 1\%$, $R_{abs} \leq 2\%$ @ 700 - 1100nm
Construction: Plate
Dimensions (mm): 75.0 x 75.0 +0.0/-0.25
Edges: Cut with 0.25mm maximum edge chip
Note: Beamsplitter-coated side is marked with a black dot
Parallelism (arcmin): ≤ 3
Reflection/Transmission Ratio (R/T): 40/60
Substrate: 
Surface Flatness (P-V): 1λ per inch
Surface Quality: 60-40
Thickness (mm): 3.00 ±0.25
Type: Standard Beamsplitter
Wavelength Range (nm): 700 - 1100

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant