

750nm, 6 x 6mm, OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock **#15-205** 3-5 DAYS



1



S\$65.25

ADD TO CART

Qty 1-9

S\$65.25

Qty 10+

S\$58.73

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):
6.00 x6.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-On Wavelength (nm): 750.00 ±15
Substrate:  BOROFLOAT®
Length (mm): 6.00
Coating: Hard Coated
Rejection Wavelength (nm): 500 - 715
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 780 - 1600
Type: Longpass Filter
Width (mm): 6.00
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 500 - 1600

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View