

75mm MegaPixel Fixed Focal Length Lens



MegaPixel Fixed Focal Length Lenses

Stock **#64-869** 3-5 DAYS



1



S\$616.25

ADD TO CART

Qty 1+

S\$616.25

Volume Pricing

[Request Quote](#)

Get Product Downloads

Field of View @ Min Working Distance (mm):
22.50

Iris Option:
Variable

Length (mm):
57.75

Horizontal Field of View, 1/2" Sensor:
5.00°

Filter Thread:
M30.5 x0.50

Maximum Diameter (mm): 35.00
Weight (g): 113.00
Maximum Rear Protrusion (mm): 4.00
Maximum Image Circle (mm): 11.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 75.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/2.8 - f/16
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View