

6.5mm Diameter x 6mm FL, PCX Condenser Lens



Stock #43-480 3-5 DAYS

[Other Coating Options](#)



1



S\$34.80

ADD TO CART

Qty 1-10

S\$34.80

Qty 11+

S\$30.45

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
6.50

Effective Focal Length EFL (mm):
6.00

Numerical Aperture NA:
0.58

Substrate: ☐

Float Glass
Focal Length Tolerance (%): ±7
Coating: Uncoated
Surface Quality: 80-50 (typical)
Center Thickness CT (mm): 3.40 ±0.2
f/#: 0.86
Bevel: Protective bevel as needed
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View