

## TECHSPEC® 8" Diameter x 40" FL Uncoated, Parabolic Mirror



Stock #32-073-000 3-5 DAYS

⊖ 1 ⊕ **S\$1,222.35**

**ADD TO CART**

Qty 1-2  
S\$1,222.35

Qty 3+  
S\$1,039.65

Volume Pricing  
[Request Quote](#)

Get Product Downloads

Substrate:   
**BOROFLOAT® SUPREMAX®**

Focal Length Tolerance (%):  
±1.5

Surface Quality:  
60-40

Surface Accuracy:

N8

**Diameter (inches):**

8.0 +0.06/-0

**Diameter (mm):**

203.20 +1.5/-0

**Effective Focal Length EFL (inches):**

40.0

**Effective Focal Length EFL (mm):**

1,016.00

**Radius of Curvature (mm):**

2,032.00

**Aperture (f#):**

f/5

**Coating:**

Uncoated

**Coating Type:**

Uncoated

**Back Surface:**

Ground

**Clear Aperture CA (mm):**

183

**Edge Thickness ET (inches):**

1.37

**Edge Thickness ET (mm):**

34.80

**Type:**

Parabolic Mirror

## Regulatory Compliance

**RoHS:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

---