

8" x 8" White Advanced Illumination Collimated Backlight

See More by [Advanced Illumination](#)



Advanced Illumination Side-Fired Collimated LED Backlight

Stock **#36-473** 3-5 DAYS

⊖ 1 ⊕

S\$1,950.25

ADD TO CART

Qty 1+

S\$1,950.25

Volume Pricing

[Request Quote](#)

Get Product Downloads

Color:
White

Model Number:
CX0808-WH11C

Operating Temperature (°C):
0 - 60

Dimensions (mm):
268.2 L x 268.2 W x 19.1 T

LED Lifetime (hours):

50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Active Area (inches): 8 x 8
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
