

80 lp/mm 1" x 3", Opal Glass Ronchi Ruling Slide



Stock **#59-548** **4 In Stock**

-

1

+

S\$459^{.20}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$459.20 each
Qty 5+	S\$437.22 each
Need More?	Request Quote

Product Downloads

General

Note:	
Pattern Location is Centered	
NIST Certification:	
No	

Physical & Mechanical Properties

Dimensional Tolerance (inches):	
±0.100	
Length (mm):	
25.40	

12.7 x25.4	Pattern Size (mm):
1.52 ±0.100	Thickness (mm):
76.20	Width (mm):
±0.001	Line Width Tolerance (µm):

Optical Properties

Vacuum Deposited Chrome	Coating:
80.00	Frequency (lp/mm):
Opal Glass	Substrate:
>3.0	Optical Density OD (Average):
40-20	Surface Quality:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

Opal Glass material has been discontinued by the manufacturer and may be available in limited quantities. [Contact us](#) for more information.

- Chrome on Opal
- Test Resolution of Reflective Systems
- High Tolerance