

TECHSPEC[®] 825nm 25mm Diameter, OD 2.0 Shortpass Filter



TECHSPEC OD 2.0 Shortpass Filters

Stock **#64-647** CLEARANCE 3-5 DAYS

-

1

+

S\$182.70

ADD TO CART

Qty 1+

S\$182.70

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-Off Wavelength (nm):
825.00

Substrate:

Fused Silica (Coming 7980)	
Coating:	Traditional Coated
Rejection Wavelength (nm):	880 - 1080
Surface Quality:	40-20
Thickness (mm):	3.00
Thickness Tolerance (mm):	±0.1
Transmission (%):	>85
Transmission Wavelength (nm):	400 - 800
Type:	Shortpass Filter
Clear Aperture (%):	80.00
Transmitted Wavefront, P-V:	λ/4
Slope Factor (%):	±3
Cut-Off Tolerance (%):	±2
Wavelength Range (nm):	400 - 1080

Regulatory Compliance

RoHS 2015:	Compliant
Reach 224:	Compliant
Certificate of Conformance:	View