

850nm 150mm Compact Light w/ Multi-Drive™



150mm Compact Light



Stock #23-941 **1 In Stock**

- 1 + \$994.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	\$994.00 each
Need More?	Request Quote

Product Downloads

General

JWL150-MD-850 **Model Number:**

LED Illuminator **Type of Illumination:**

Smart Vision Lights LLC **Manufacturer:**

Ring Light **Geometry:**

Constant or Strobed
Illumination Mode:

Physical & Mechanical Properties

158.75 W x 84.25 H x 40.18 D (58.15 D Including Connector)
Dimensions (mm):

589.67
Weight (g):

65.38W x 65.38W
Active Area (mm):

Optical Properties

IR
Color:

850
Wavelength (nm):

500 - 2,000
Working Distance (mm):

Electrical

30 - ∞
Strobe Duration (µs):

Hardware & Interface Connectivity

5-pin M12 connector
Connector:

24 VDC ± 5%
Input Voltage (V):

Threading & Mounting

T-Slot for M6 Nut
Mount:

Environmental & Durability Factors

-10° to +40°
Operating Temperature (°C):

IP65
Environmental Rating:

Regulatory Compliance

[View](#)
Certificate of Conformance:

Product Details

- Direct Connect and Control via Camera's Trigger Output
- Built-In Multi-Drive™ Technology
- T-Slots for Mounting

Smart Vision Lights Compact Ring Lights are IP65-rated brightfield lights featuring a working distance of 500-mm to 2000-mm that can be directly connected to a camera for control via the trigger output. Built-in Multi-Drive™ technology, which offers both continuous operation and OverDrive™ mode, delivers up to 6 times the continuous power with a low-latency response and fast strobe durations down to 10mS. These lights feature a batwing design that illuminates a larger area than built-in lighting systems and produces a greater light output making them ideal to use alongside polarizers, diffusers, and other optical elements that reduce light output. Smart Visions Lights Illumination products offer an industry-leading 10-year limited warranty.