

9X English Linear Scale & Comparator Set



Stock #02-047 **5 In Stock**

- 1 + **S\$246⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	S\$246.50 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Inch Reticle

Type:

Kellner-type / AR coated

Type of Optics:

Note:	
Nylon case (#36-286) is sold separately.	
Physical & Mechanical Properties	
0.75	Field of View (inches):
0.68	Diameter of Included Lens (inches):
27.00	Diameter of Compatible Reticle (mm):
1.25	Height (inches):
40.8	Weight (g):
Optical Properties	
0.75	Working Distance (inches):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Clear Base Admits Light
- High Power, Wide Field
- Reticle Included

Excellent for determining paper quality and ink absorption. Ideal for proofreaders. The transparent acrylic base rests directly on work for clear, close-up examinations. Base admits light to subject under view. 9X is Kellner-type, color-corrected, three-element lens system.

Twist focus with lock-ring for permanent setting. Contact reticle adapter ring on base accepts all 27mm diameter reticles.

Note: Nylon case (#36-286) is sold separately.

Reticle Description

Straight line scales for critical measurement in either English (inch) or metric. English/inch: 0 to 0.75" scale in 0.005" increments, numbered every 0.025 increments. Metric: 0 to 20mm scale in 0.1mm increments, numbered every 1.0mm.