

[See all 3 Products in Family](#)

Achromatic Lens 6.25mm Dia. x 35mm FL, Uncoated



Stock #32-306 **CLEARANCE** 7 In Stock

- 1 + \$18⁹⁰

ADD TO CART

Volume Pricing

Qty 1+	\$18.90 each
Need More?	Request Quote

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

2.30 **Center Thickness CT 1 (mm):**

0.90 **Center Thickness CT 2 (mm):**

6.2500000000 +0.00/-0.05 **Diameter (mm):**

Edge Thickness ET (mm):

2.86

Center Thickness Tolerance (mm):
±0.1

Centering (arcmin):
1.00

Optical Properties

Back Focal Length BFL (mm):
33.59

Coating:
Uncoated

Effective Focal Length EFL (mm):
35.0000000000

Substrate:
[N-BK7 / N-SF5](#)

Numerical Aperture NA:
0.0800000000

Radius R₁ (mm):
23.1400000000

Radius R₂ (mm):
-14.51

Radius R₃ (mm):
-38.86

Surface Quality:
40-20

Focal Length Tolerance (%):
±2

Focal Length Specification Wavelength (nm):
632.8

f#:
5.6

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Discounts up to 80% Off
- Quantities Extremely Limited
- Final Sale, No Returns

Shop the EO Mega Clearance presentations for the hottest deals on component-level products. Quickly browse the best optics, [imaging](#), and [photronics](#) deals you will ever see. Quantities are extremely limited and are sold on a first-come-first-serve basis.

Hurry, while supplies last. EO Mega Clearance products will never be sold again. Check out our standard [clearance products](#) for even more deals!

All products are final sale; EO will not accept returns. No additional information is available other than what is listed.

Compatible Mounts