


Adapter Plate for #55-029



#55-038



Stock **#55-038** 10 In Stock

-

1

+

S\$54^{.25}

ADD TO CART

Volume Pricing	
Qty 1-9	S\$54.25 each
Qty 10+	S\$48.72 each
Need More?	Request Quote

Product Downloads

General

Type:

Adapter Brackets & Plates

Physical & Mechanical Properties

Length (inches):

2.36

Length (mm):

60.00	
60 x 60 x 7	Dimensions (mm):
Threading & Mounting	
Mounting Threads: (4) M4 x 0.7, (4) M3 x 0.5, (4) M2 x 0.4, (1) 1/4-20	
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Precision Micrometer Drive and Manual Drive Options
- 360° Coarse Rotation
- Micrometer Drive Models Provide ±5° Fine Rotation
- Black Anodized Aluminum Construction

Metric Rotary Stages feature slide-fit guide system, enabling 360° course rotation. Micrometer drive models feature a precision metric micrometer and a switchable clamp mechanism to change between course and fine movements for precise ±5° angular adjustment at any position. The manual drive model provides a smooth manual adjustment with 360° coarse movement, 1° increments. Metric Rotary Stages feature a locking mechanism to fix the stage position. For breadboard mounting, use the [Metric Base Plates](#).

Technical Information

