

Allied Vision Guppy Pro F-201 1/1.8" CCD Monochrome Camera

See More by [Allied Vision](#)



Stock **#68-569** [CONTACT US](#)

[Similar Cameras](#)

- 1 + **\$S\$2,451.95**

ADD TO CART

Qty 1+
\$S\$2,451.95

Volume Pricing
Request Quote

Get Product Downloads

Video Output:
FireWire.b

Type:
Monochrome Camera

Manufacturer:
Allied Vision

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#68-585](#)

Image Buffer:

64MB
Camera Family: Guppy Pro
Model Number: F-201
Imaging Sensor: Sony ICX274
Type of Sensor: Progressive Scan CCD
Type of Shutter: Global
Camera Sensor Format: 1/1.8"
Resolution (MegaPixels): 2.00
Pixels (H x V): 1,624 x 1,234
Pixel Size, H x V (µm): 4.4 x 4.4
Sensing Area, H x V (mm): 7.2 x 5.4
Frame Rate (fps): 14.00
Pixel Depth: 12 bit
Exposure Time: Via Software
Connector: FireWire, IEEE 1394b
Power Supply: Power over FireWire, or with Power Supply Sold Separately. USA: #15-281 Europe: #15-281 Japan: #15-281 China: #15-281
Power Consumption (W): <3.5 (12VDC External Power Supply)
GPIOs: 1 configurable opto-coupled input, 3 configurable opto-coupled outputs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 29 x 29 x 29 (excludes connectors and lens mount)
Weight (g): 70
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): +5 to +45
Storage Temperature (°C): -10 to +70
GPIO Connector Type: 12-pin Hirose (HR10)
Machine Vision Standard: IIDC Standard v1.31
Power Requirement: Supplied via IEEE-1394 cable or 12-pin Hirose

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

