

Hoya B440 (UV-VIS) 12mm Dia., Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#48-632** 3-5 DAYS

- 1 +

S\$53.65

ADD TO CART

Qty 1-10

S\$53.65

Qty 11+

S\$47.85

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.00

Center Wavelength CWL (nm):
440.00

Density (g/cm³): 2.70
Full Width-Half Max FWHM (nm): 85.00
Glass/Filter Number: Hoya B440
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Blue-Green
Surface Quality: 60-40
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Bandpass Filter
Wavelength: UV-Vis
Parallelism (arcmin): ≤1
Dimensional Tolerance (mm): +0/-0.25

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View