

Lux/Footcandle Calibrated Light Meter



Stock #57-476 [CONTACT US](#)

- 1 + **\$848.25**

ADD TO CART

Qty 1+
\$848.25

Volume Pricing
Request Quote

Get Product Downloads

Operating Temperature (°C): 0 to +55
Range: 0 - 400,000 Lux 0 - 40,000 FC
Type: Lux/Footcandle Model
Weight (g): 150.00
Storage Temperature (°C): -20 to +70

Dimensions (mm): 141 x 59 x 25
Operating Lifetime (hours): Battery ON: 300 Battery OFF: 4 Years
Power Supply: 9 V Alkaline Battery Included
Display Accuracy (%): Overall: ±5 Photopic: >1.0 Cosine Error: <±1.0 up to ±85° AOI

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View