

[See all 58 Products in Family](#)

Basler ace acA5472-17um USB 3.0 Monochrome Camera

See More by [Basler](#)



Basler ace USB 3.0 Cameras (Front)



Stock **#11-502** [CONTACT US](#)

[Similar Cameras](#)

- 1 + **S\$1,022⁰⁰**

ADD TO CART

Volume Pricing

Qty 1+	S\$1,022.00 each
Need More?	Request Quote

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Camera **Type:**

acA5472-17um **Model Number:**

Basler
ace

Manufacturer:
Camera Series:

Physical & Mechanical Properties

29.3 x 29 x 29 (excludes connectors and lens mount)

Dimensions (mm):
Weight (g):

80

Housing:

Full

Sensor

Not Specified

Image Buffer:

1"

Sensor Format:

20.00

Resolution (Megapixels):

17.00

Frame Rate (fps):

5,472 x 3,648

Pixels (H x V):

2.4 x 2.4

Pixel Size, H x V (µm):

13.13 x 8.76

Sensing Area, H x V (mm):

Sony IMX183

Imaging Sensor:

Progressive Scan CMOS

Type of Sensor:

Rolling

Shutter Type:

10/12 bit

Pixel Depth:

Freely Programmable

Exposure Time:

72.0

Dynamic Range (dB):

USB3 Vision v1.0

Machine Vision Standard:

Electrical

2.9

Power Consumption (W):

Hardware & Interface Connectivity

USB 3.0

Interface:

USB 3.0, Micro-B with Screw Locks

Connector:

Power over USB

Power Supply:

1 opto-coupled input line, 1 opto-coupled output line,
2 general purpose I/O (GPIO) lines

GPIOs:

Hardware Trigger (GPIO), Software Trigger, or Free-Run

Synchronization:

Back Panel

Interface Port Orientation:

6-pin Hirose (HR10)

GPIO Connector Type:

Software Driver: Windows, Linux - 32 and 64 bit

Operating System:

Threading & Mounting

C-Mount

Mount:

1/4-20 with Tripod Mount Adapter [#88-517](#)

Mounting Threads:

Environmental & Durability Factors

0 to +50

Operating Temperature (°C):

-20 to +80 **Storage Temperature (°C):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**


Compliant **Reach 235:**

Product Details

- High Speed USB 3.0 Interface
- Ultra-Small Form Factor
- Fully USB3 Vision Compliant

Basler ace USB 3.0 Cameras are an ideal choice for analog camera users looking to upgrade to digital, or for FireWire or USB 2.0 users looking for faster data transfer rates. Basler ace USB 3.0 Cameras are fully USB3 Vision compliant and feature a small, 29 x 29mm form factor that makes them easy drop-in replacements for many analog, FireWire, or USB 2.0 cameras. Additionally, these USB 3.0 cameras feature screw-locking USB 3.0 ports for increased ruggedness in demanding applications, such as factory floor use. All cameras include the Basler Pylon SDK software and driver.

Technical Information



MT9P031 Sensor QE Curve