



SCHOTT BG25, 25.4mm Dia., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#84-901** 3-5 DAYS

-

1

+

S\$68.15

ADD TO CART

Qty 1-10
S\$68.15
Qty 11+
S\$59.45
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.40

Center Wavelength CWL (nm):
400.00

Density (g/cm³):

2.56
Glass/Filter Number: SCHOTT BG25
Coating: Uncoated
Color: Blue-Violet
Surface Quality: 80-50
Thickness (mm): 3.00 ±0.2
Type: Bandpass Filter
Wavelength: UV-VIS
Note: Intense UV radiation can cause a reduction in transmission
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View