



SCHOTT BG38, 25.4mm Dia., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#46-433** [CONTACT US](#)

-

1

+

S\$68.15

ADD TO CART

Qty 1-10
S\$68.15
Qty 11+
S\$59.45
Volume Pricing
Request Quote

Get Product Downloads
Diameter (mm): 25.40
Center Wavelength CWL (nm): 470.00
Density (g/cm³):

2.62
Glass/Filter Number: SCHOTT BG38
Coating: Uncoated
Color: Blue-Green
Surface Quality: 80-50
Thickness (mm): 3.00 ±0.2
Type: Bandpass Filter
Wavelength: VIS
Note: Can also be used as a shortpass filter with a cut-off wavelength of 645nm
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View
