

TECHSPEC[®] 30mm, C-Mount Ring Mount, 1/4-20 Tapped Hole



Stock #52-930 8 In Stock

-

1

+

S\$154^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$154.00 each
Qty 5-9	S\$136.36 each
Qty 10-25	S\$126.28 each
Need More?	Request Quote

Product Downloads

General	
Post Mounting Adapter	Function:
Physical & Mechanical Properties	
12.70	Thickness (mm):
Black Anodized Aluminum (6061 T6)	Construction:

48.0	Outer Diameter (mm):
30.0	Inner Diameter (mm):
Threading & Mounting	
21.75	Mounting Flat to Center (mm):
C-Mount	Thread Type:
1/4-20	Compatible Post:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Allow for Post Mounting C, S, and T-Mount Tube System Assemblies
 - 1/4-20 or M6 Tapped Mounting Options
 - Black Anodized Aluminum Construction
- TECHSPEC® C, S, and T-Mount Ring Mounts feature a screw closure and accept 30mm, 16mm, and 48mm outer diameter tubes and barrels, respectively. Ring mounts are available with either 1/4-20 or M6 tapped mounting threads. TECHSPEC C, S, and T-Mount Ring Mounts are ideal for quickly integrating C, S, or T-Mount tube assemblies into any benchtop system. A black anodized construction reduces reflections within a system.

Technical Information

