

TECHSPEC[®] C-Mount Extension Tube Kit



Stock **#54-668** [CONTACT US](#)

-

1

+

S\$513^{.80}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$513.80 each
Qty 5-9	S\$453.18 each
Qty 10-25	S\$417.34 each
Need More?	Request Quote

Product Downloads

General

Type:

C-Mount Kit

Contents of Kit:

5mm: [#54-628](#), 10mm: [#54-629](#), 15mm: [#54-630](#),
50mm: [#54-632](#), 100mm: [#54-633](#)

Function:

Extension Tube (Fixed)

Physical & Mechanical Properties

30.0	Outer Diameter (mm):
22.0	Clear Aperture CA (mm):
Threading & Mounting	
C-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

Technical Information

