

[See all 66 Products in Family](#)

Cat 6a M12 to RJ45 Ethernet Dragchain Cable, IP65/67, 15m

See More by [IDS Imaging Development Systems](#)



Stock #19-700 **1 In Stock**

⊖ 1 ⊕ S\$343⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$343.00 each
Need More?	Request Quote

Product Downloads

General

Camera Accessory **Type:**
Dragchain, M12 to RJ45 Connector **Note:**

Hardware & Interface Connectivity

15 **Length of Cable (m):**
Cat 6a, M12 **Connector:**

Regulatory Compliance

[Exempt](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Contains SVHC\(s\)](#)

REACH 241:

Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.