

[See all 16 Products in Family](#)

CM3-U3-13Y3C-S-BD 1/2" Chameleon®3 Monochrome Camera

See More by [Teledyne FLIR](#)



USB 3.0 FLIR Chameleon Camera



Stock **#70-324** 1 In Stock

-

1

+

S\$581⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$581.00 each
Need More?	Request Quote

Product Downloads

Monochrome	Spectrum:
General	
Monochrome Camera	Type:
CM3-U3-13Y3M-S-BD	Model Number:
Manufacturer:	

FLIR	
Chameleon®3	Camera Series:
Physical & Mechanical Properties	
40 × 31 (board level)	Dimensions (mm):
27.9	Weight (g):
Board Level	Housing:
Sensor	
16MB	Image Buffer:
1/2"	Sensor Format:
1.30	Resolution (Megapixels):
149.00	Frame Rate (fps):
1,280 x 1,024	Pixels (H x V):
4.8 x 4.8	Pixel Size, H x V (µm):
6.14 x 4.92	Sensing Area, H x V (mm):
ON Semi PYTHON 1300	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
10 bit	Pixel Depth:
10µs - 1s	Exposure Time:
56.19	Dynamic Range (dB):
USB3 Vision v1.0	Machine Vision Standard:
Hardware & Interface Connectivity	
USB 3.0	Interface:
USB 3.1 Gen 1, Micro-B with Screw Locks	Connector:
Power over USB or via GPIO	Power Supply:
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports	GPIOs:
Hardware Trigger (GPIO)	Synchronization:
Side Panel	Interface Port Orientation:
9-pin JST	GPIO Connector Type:
Threading & Mounting	
S-Mount (M12 x 0.5)	Mount:
¼-20 with Tripod Mount Adapter #88-210	Mounting Threads:
Environmental & Durability Factors	
0 to +45	Operating Temperature (°C):
-30 to +60	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- USB3 Connectivity
- Lightweight Construction
- Compact Design



Teledyne FLIR IIS Chameleon®3: Easy integration with USB3

Ccompact USB3 cameras

The **Chameleon®3** camera line combines popular CCD and CMOS image sensors with the ease of use of USB 3.0, with a compact form factor and camera sensor resolutions ranging from 1.3 MP to 5.0 MP.

These cameras feature a compact 44 x 35 x 19.5mm lightweight metal case designed for reliability. They offer multiple mounting points and a locking USB 3.0 connection. The camera includes an on-camera frame buffer for image retransmission and an optoisolated GPIO with a locking connection.

Features

- Compact form factor
- On-camera image processing: color interpolation, gamma, & LUT
- Data interface: USB3
- 16 MByte frame buffer
- LED Status indicator
- Spinnaker SDK and FlyCapture interfaces

Applications

- Life science instrumentation
- Factory automation
- Biometrics kiosk solutions
- Ophthalmoscopy
- 3D scanning
- Automated optical inspection