


Coarse/Fine Movement, 1/4-20, Rack & Pinion



#54-794

Stock **#54-794** 6 In Stock

-

1

+

S\$812⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$812.00 each
Need More?	Request Quote

Product Downloads

General

Rack and Pinion Mount	Type:
1/4-20 Stud	Note:
Coarse/Fine Movement	Type of Adjustment:

Physical & Mechanical Properties

Rack and Pinion Block: 50 H x 30 W x 50 L	Dimensions (mm):
---	------------------

35 (+23/-12) in Y	Travel (mm):
25.5 coarse, 3.2 fine	Travel Per Knob Rotation (mm):
2.00	Load Capacity (kg):
Linear (Y)	Type of Movement:
51.00	Optical Centerline from Post (mm):

Threading & Mounting

3/4" Diameter Post 1/4-20 Tapped Hole	Mounting Post Hole and Thread:
--	--------------------------------

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Coarse or Fine Motion Available
 - Thru Holes for Integrating Lenses
 - 1/4-20 Stud for Mounting Cameras
 - [Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) also Available
- Rack and Pinion Focusing Mounts for Imaging Systems add additional focus ability to imaging systems. Thru Holes are ideal for use with [TECHSPEC® VZM™ Zoom Imaging Lenses](#) or other imaging lenses. Rack and Pinion Movement with 1/4-20 stud can be used with any compatible camera or imaging lens. Rack and Pinion Focusing Mounts for Imaging Systems are offered with either coarse or fine motion.[Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) are also available.