

Coarse/Fine Movement, 1/4-20 w/ Rotation, Rack & Pinion



#59-322

Stock **#59-322** 9 In Stock

-

1

+

S\$940⁹¹

ADD TO CART

Volume Pricing	
Qty 1+	S\$940.91 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General	
Rack and Pinion Mount	Type:
1/4-20 Stud	Note:
Coarse/Fine Movement	Type of Adjustment:

Physical & Mechanical Properties	
	Dimensions (mm): Rack and Pinion Block: 50 H x 30 W x 50 L
	Travel (mm): 35 (+23/-12) in Y
	Travel Per Knob Rotation (mm): 25.5 coarse, 3.2 fine
	Load Capacity (kg): 2.00
	Type of Movement: Linear (Y), Rotation
	Optical Centerline from Post (mm): 51.00
Threading & Mounting	
	Mounting Post Hole and Thread: 3/4" Diameter Post 1/4-20 Tapped Hole
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- Coarse or Fine Motion Available
- Thru Holes for Integrating Lenses
- 1/4-20 Stud for Mounting Cameras
- [Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) also Available

Rack and Pinion Focusing Mounts for Imaging Systems add additional focus ability to imaging systems. Thru Holes are ideal for use with [TECHSPEC® VZM™ Zoom Imaging Lenses](#) or other imaging lenses. Rack and Pinion Movement with 1/4-20 stud can be used with any compatible camera or imaging lens. Rack and Pinion Focusing Mounts for Imaging Systems are offered with either coarse or fine motion. [Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) are also available.