

Coarse/Fine Movement, 50mm Dia Thru w/ Rotation, Rack & Pinion



#59-321

Stock **#59-321** 6 In Stock

-

1

+

S\$903⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$903.00 each
Need More?	Request Quote

Product Downloads

General

Rack and Pinion Mount	Type:
50 mm Diameter Thru-Hole	Note:
Coarse/Fine Movement	Type of Adjustment:

Physical & Mechanical Properties

Rack and Pinion Block: 50.8 H x28.6 W x50.8 L	Dimensions (mm):
---	------------------

35 (+23/-12) in Y	Travel (mm):
1.31	Weight (lbs):
25.5 coarse, 3.2 fine	Travel Per Knob Rotation (mm):
2.00	Load Capacity (kg):
Linear (Y), Rotation	Type of Movement:
100.00	Optical Centerline from Post (mm):

Threading & Mounting

3/4" Diameter Post 1/4-20 Tapped Hole	Mounting Post Hole and Thread:
--	--------------------------------

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Coarse or Fine Motion Available
- Thru Holes for Integrating Lenses
- 1/4-20 Stud for Mounting Cameras
- Imaging System Bases, Stainless Steel Posts, and Accessories also Available

Rack and Pinion Focusing Mounts for Imaging Systems add additional focus ability to imaging systems. Thru Holes are ideal for use with [TECHSPEC® VZM™ Zoom Imaging Lenses](#) or other imaging lenses. Rack and Pinion Movement with 1/4-20 stud can be used with any compatible camera or imaging lens. Rack and Pinion Focusing Mounts for Imaging Systems are offered with either coarse or fine motion.[Imaging System Bases, Stainless Steel Posts](#), and [Accessories](#) are also available.