

[See all 2 Products in Family](#)

Concentric Square Target On White Ivory Soda Lime Glass



#58-773

Stock **#58-773** [CONTACT US](#)

-

1

+

\$S\$1,190^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	\$S\$1,190.00 each
Qty 5+	\$S\$1,130.78 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
1, 2, 3, 4, 5, 10, 15, 20, 30, 40, 50	Pattern Size (mm):
76.2 x 76.2	Dimensions (mm):
3.17	Thickness (mm):
±0.002	Line Width Tolerance (mm):

Optical Properties

Coating:	
Vacuum Deposited Chromium Oxide (specular reflectivity <5% @ 550nm)	
Substrate:	
White Ivory Soda Lime Glass	
Surface Quality:	
40-20	
Surface Flatness (P-V):	
0.1mm	

Regulatory Compliance

RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 240:	
Compliant	

Product Details

- For Calibration of Measurement Software
- NIST Traceable Certificate of Accuracy Included
- 1mm to 50mm Squares

Concentric Square Targets provide an accurate means of calibrating measurement software for image processing. The squares vary in dimensions to accommodate different fields of view. The square targets are NIST Traceable Certificate of Accuracy included. Concentric Square Targets are offered in 1 to 50mm pattern sizes. Included in the packaging is a serialized NIST Traceable Certificate of Accuracy per ML-STD-45662A