

Constant, White, High Intensity LED Spot Light

See More by [Advanced Illumination](#)



Stock **#86-429** [CONTACT US](#)

- 1 + **S\$829.40**

ADD TO CART

Qty 1+

S\$829.40

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:

White

Height (mm):

26.0

Model Number:

SL147-WHI-IC

Operating Voltage (V):

24.00

Dimensions (mm): 66.7 L x 62.0 W
Mounting Threads: M4 Nut Channel for Mounting
Weight (g): 122.5
Working Distance (inches): 6 - 24
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Power Requirement: 90 - 264 V AC @ 47 - 63 Hz
Length of Cable (m): 1.5
Field Coverage (mm): 65.00
Maximum Trigger Frequency (Hz): 30.00
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)