

Digital Photometer



Stock #54-038 3-5 DAYS

-

1

+

S\$433.55

ADD TO CART

Qty 1+

S\$433.55

Volume Pricing

[Request Quote](#)

Get Product Downloads

Range:
19.99µW, 199.9µW, 1.999mW, 19.99mW

Dimensions (mm):
Head: 26 Diameter x 38 L
160 L x 95 W x 65 H

Power Requirement:
Two 9 V Batteries (Included)

Maximum Incident Beam Power (mW):
20

Meter Accuracy (%):
±10

Active Area (cm²):
1.00

Output Wavelength (nm):
632.8

Regulatory Compliance

RoHS:
Not Compliant

Certificate of Conformance:
[View](#)