

E-Series D-Shape Knife Edge Kinematic Mirror Mount



Stock **#21-063** 7 In Stock

-

1

+

S\$141⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-9	S\$141.40 each
Qty 10+	S\$134.40 each
Need More?	Request Quote

Product Downloads

General	
Adjustable - Tip-Tilt	Type:
D-Shaped	Type of Optics:
2	Number of Adjustment Screws:

Physical & Mechanical Properties	
23	Clear Aperture CA (mm):
Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings	Construction:
±3.5	Fine Tilt Angle (°):
±3.5	Fine Tip Angle (°):
0.25	Adjustment Screw Pitch (mm):
7	Max. Thickness of Compatible Optics (mm):
38.10	Optical Axis Height (mm):
Threading & Mounting	
25.40	Size of Compatible Optics (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Ideal Mount for [1" Knife-Edge Pickoff Mirrors](#)
 - Economic Price
 - M6 x 0.25 (101.6 TPI) Adjustment Screws
- E-Series Kinematic D-Shape Optical Mirror Mounts offer many high value features essential for mounting [1" \(25.4mm\) diameter Knife-Edge Pickoff Mirrors](#). The mounts are offered with 2 screws for tip and tilt optical adjustment and alignment (±3.5°). The M6 x 0.25 (101.6 TPI) adjustment screws provide smooth movement and can be driven by hand or by Allen key (2mm key size). The adjustment screw knobs are removable to create a more compact form factor. E-Series Kinematic D-Shape Optical Mirror Mounts feature mounting holes with both a counterbore designed to accommodate M4 or 8-32 mounting hardware, and M6 x 1.0 internal threads for increased mounting versatility and direct compatibility to [TECHSPEC® Stainless Steel Mounting Posts](#) and [Pedestal Posts](#).