

TECHSPEC® Elliptical Mirror 66.68mm Minor Axis UV Enhanced Aluminum



Stock #43-580 **3 In Stock**

- 1 + S\$575⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | S\$575.40 each |
| Qty 6-25 | S\$460.60 each |
| Qty 26-49 | S\$431.20 each |
| Need More? | Request Quote |

Product Downloads

General

Flat Mirror **Type:**

Flatness specification is Peak to Valley **Note:**

Physical & Mechanical Properties

±0.060 **Thickness Tolerance (inches):**

| | | | | | | | | | |
|---|-------|--------|-------|---------|---------|---------|---------|---------|---------|
| B | 12.70 | 17.96 | 3.81 | #32-270 | #32-271 | #43-573 | #32-272 | #32-273 | #89-454 |
| B | 22.23 | 31.42 | 6.35 | #32-093 | #30-836 | #43-574 | #32-131 | #32-085 | #89-455 |
| B | 26.97 | 38.15 | 6.35 | #32-094 | #30-837 | #43-575 | #32-132 | #32-086 | #89-456 |
| A | 31.75 | 44.91 | 9.53 | #32-095 | #30-205 | #43-576 | #32-133 | #32-087 | #89-457 |
| A | 38.10 | 53.87 | 9.53 | #32-096 | #30-258 | #43-577 | #32-134 | #32-088 | #89-458 |
| A | 47.63 | 67.36 | 11.68 | #32-097 | #30-840 | #43-578 | #32-135 | #32-089 | #89-459 |
| B | 57.15 | 80.82 | 15.88 | #32-098 | #41-131 | #43-579 | #32-136 | #32-090 | #89-460 |
| B | 66.68 | 94.28 | 15.88 | #32-099 | #42-583 | #43-580 | #32-137 | #32-091 | #89-461 |
| B | 76.20 | 107.77 | 19.05 | #32-100 | #42-584 | #43-581 | #32-138 | #32-092 | #89-462 |

