

Fiber Optic Taper For 18mm to 1/2" Sensor



Stock #55-136 3-5 DAYS

⊖ 1 ⊕ **S\$1,857.45**

ADD TO CART

Qty 1+
S\$1,857.45

Volume Pricing
Request Quote

Get Product Downloads

Diameter Tolerance (mm):
±0.5, Large End

Distortion (%):
3.00

Substrate: ☐
[Schott 24 Glass with EMA](#)

Height (mm):
20.00

Diameter of Large End (mm):
20.00

Numerical Aperture NA: 1.00
Operating Temperature (°C): -10 to +300
Resolution: 102 lp/mm
Size Ratio: 18:½" CCD
Size of Small End (mm): 6.4 x 4.8
Surface Quality: 30-20
Thickness Tolerance (mm): ±0.1
Resolving Power (µm): 6.00
Dimensional Tolerance (mm): ±0.1
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 6.8
Core/ Clad Ratio: 70 / 30

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View