

3/4" Dia Stainless Posts, Horizontal Arm 24"



Stock #52-607 **3 In Stock**

S\$166^{.60}

ADD TO CART

Volume Pricing

Qty 1+	S\$166.60 each
Need More?	Request Quote

Product Downloads

General

Mounting Post **Type:**

Physical & Mechanical Properties

609.6 **Length (mm):**

2.25 **Weight (lbs):**

24.0 **Length (inches):**

Diameter (inches):

Threading & Mounting

1/4-20 Pin, 5/16-18 Pin **Mounting Threads:**

Regulatory Compliance

Compliant **RoHS 2015:**

Compliant **Reach 224:**

View **Certificate of Conformance:**

Product Details

- Posts for Integration into Imaging Systems
- Vertical Posts Thread to Bases and Platforms
- Horizontal Arms Thread to Posts and Microscope Head Mounts
- [Rack and Pinion Focusing Mounts](#), and [Accessories](#) also Available

Stainless Steel Posts for Imaging Systems are used for constructing and supporting imaging systems. Vertical posts can be threaded directly into bases or platforms and include a steel collar with a set screw. Horizontal arms can be used with a 90° angle mount, on vertical posts, or with a breadboard adapter. Stainless Steel Posts for Imaging Systems are 3/4 of an inch in diameter and are offered in lengths ranging from 9.0 inches (228.6mm) to 24.0 inches (609.6mm). The mounting threads for these posts are available threaded on one end with 3/4"-16 male or threaded on both ends with a combination of 1/4"-20 and 5/16"-18 pins.
