

## 3/4" Dia Stainless Posts, Vertical Post 18"



Stock #39-353 **8 In Stock**

⊖ 1 ⊕ **S\$151<sup>20</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>S\$151.20</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Mounting Post **Type:**

### Physical & Mechanical Properties

457.2 **Length (mm):**

1.75 **Weight (lbs):**

18.0 **Length (inches):**

**Diameter (inches):**

## Threading & Mounting

3/4-16 Male (One End) **Mounting Threads:**

---

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

---

**Reach 250:**  
[Compliant](#)

---

## Product Details

- Posts for Integration into Imaging Systems
- Vertical Posts Thread to Bases and Platforms
- Horizontal Arms Thread to Posts and Microscope Head Mounts
- [Rack and Pinion Focusing Mounts](#), and [Accessories](#) also Available

Stainless Steel Posts for Imaging Systems are used for constructing and supporting imaging systems. Vertical posts can be threaded directly into bases or platforms and include a steel collar with a set screw. Horizontal arms can be used with a 90° angle mount, on vertical posts, or with a breadboard adapter. Stainless Steel Posts for Imaging Systems are 3/4 of an inch in diameter and are offered in lengths ranging from 9.0 inches (228.6mm) to 24.0 inches (609.6mm). The mounting threads for these posts are available threaded on one end with 3/4"-16 male or threaded on both ends with a combination of 1/4"-20 and 5/16"-18 pins.

---