



Hoya G545 (VIS) 25.4mm Dia., Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#34-441** [CONTACT US](#)

[-](#) 1 [+](#)

S\$92.80

ADD TO CART

Qty 1-10
S\$92.80
Qty 11+
S\$82.65
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40

Center Wavelength CWL (nm):
545.00

Density (g/cm³): 3.10
Full Width-Half Max FWHM (nm): 47.00
Glass/Filter Number: Hoya G545
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Green
Surface Quality: 80-50
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Bandpass Filter
Wavelength: VIS
Parallelism (arcmin): ≤1
Dimensional Tolerance (mm): +0/-0.25

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View