



# Hoya G550 (VIS) 50.8mm Square, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock #34-454 3-5 DAYS

- 1 +

S\$159.50

ADD TO CART

Qty 1-10

S\$159.50

Qty 11+

S\$140.65

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):  
50.8 x 50.8

Center Wavelength CWL (nm):  
550.00

|                                                                  |
|------------------------------------------------------------------|
| <div>Density (g/cm³):<br/>2.58</div>                             |
| <div>Full Width-Half Max FWHM (nm):<br/>180.00</div>             |
| <div>Glass/Filter Number:<br/><a href="#">Hoya G550</a></div>    |
| <div>Substrate: <input type="checkbox"/><br/>Colored Glass</div> |
| <div>Length (mm):<br/>50.80</div>                                |
| <div>Coating:<br/>Uncoated</div>                                 |
| <div>Color:<br/>Green</div>                                      |
| <div>Surface Quality:<br/>80-50</div>                            |
| <div>Thickness (mm):<br/>2.50</div>                              |
| <div>Thickness Tolerance (mm):<br/>±0.2</div>                    |
| <div>Type:<br/>Bandpass Filter</div>                             |
| <div>Wavelength:<br/>VIS</div>                                   |
| <div>Width (mm):<br/>50.80</div>                                 |
| <div>Parallelism (arcmin):<br/>≤2</div>                          |
| <div>Dimensional Tolerance (mm):<br/>+0/-0.25</div>              |

## Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS 2015:<br/><a href="#">Exempt</a></div>                |
| <div>Reach 224:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |

---